

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255235

Luminaire Tested: P3AS17R659035DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1255235  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R659035DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1639.1 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255235  
CATALOG NUMBER: P3AS17R659035DE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1255235  
 CATALOG NUMBER: P3AS17R659035DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	400538
5°	376975
10°	372182
15°	365609
20°	345200
25°	320389
30°	249026
35°	144072
40°	58052
45°	26731
50°	10405
55°	4052
60°	3508
65°	3424
70°	3398
75°	3389
80°	3410
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26731 cd/sqm



TEST NUMBER: P1255235  
 CATALOG NUMBER: P3AS17R659035DE010 E3CB1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.8	9.9
10°-20°	449.7	27.4
20°-30°	588.7	35.9
30°-40°	341.0	20.8
40°-50°	73.0	4.5
50°-60°	11.9	0.7
60°-70°	6.6	0.4
70°-80°	3.9	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1201.3	73.3
0°-40°	1542.3	94.1
0°-60°	1627.2	99.3
0°-90°	1639.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1639.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1827	
5°	1713	163
15°	1610	450
25°	1324	589
35°	538	341
45°	86	73
55°	11	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1255235  
CATALOG NUMBER: P3AS17R659035DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1826.6
2.5°	1774.9
5°	1712.6
7.5°	1687.4
10°	1671.5
12.5°	1649.0
15°	1610.5
17.5°	1550.9
20°	1479.3
22.5°	1411.7
25°	1324.2
27.5°	1177.1
30°	983.5
32.5°	762.2
35°	538.2
37.5°	340.7
40°	202.8
42.5°	127.3
45°	86.2
47.5°	55.7
50°	30.5
52.5°	14.6
55°	10.6
57.5°	9.3
60°	8.0
62.5°	8.0
65°	6.6
67.5°	5.3
70°	5.3
72.5°	4.0
75°	4.0
77.5°	2.7
80°	2.7
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0

(END OF REPORT)