

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254404

Luminaire Tested: P3AS09R559035DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559035DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 821.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254404

CATALOG NUMBER: P3AS09R559035DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1254404

CATALOG NUMBER: P3AS09R559035DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225442
5°	223156
10°	215494
15°	199207
20°	171888
25°	135758
30°	96319
35°	62105
40°	37298
45°	21025
50°	11292
55°	4014
60°	3640
65°	3528
70°	3398
75°	3219
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21025 cd/sqm

TEST NUMBER: P1254404

CATALOG NUMBER: P3AS09R559035DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	11.6
10°-20°	242.6	29.6
20°-30°	254.3	31.0
30°-40°	148.3	18.1
40°-50°	55.5	6.8
50°-60°	13.0	1.6
60°-70°	6.7	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.3	72.1
0°-40°	740.6	90.2
0°-60°	809.2	98.6
0°-90°	821.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1028	
5°	1014	95
15°	878	243
25°	561	254
35°	232	148
45°	68	56
55°	10	13
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1254404

CATALOG NUMBER: P3AS09R559035DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1028.1
2.5°	1025.1
5°	1013.8
7.5°	995.7
10°	967.8
12.5°	928.7
15°	877.5
17.5°	812.7
20°	736.6
22.5°	651.5
25°	561.1
27.5°	468.5
30°	380.4
32.5°	300.5
35°	232.0
37.5°	176.2
40°	130.3
42.5°	93.4
45°	67.8
47.5°	49.0
50°	33.1
52.5°	18.8
55°	10.5
57.5°	9.0
60°	8.3
62.5°	7.5
65°	6.8
67.5°	6.0
70°	5.3
72.5°	4.5
75°	3.8
77.5°	3.0
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)