

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254431

Luminaire Tested: P3AS09R609035DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609035DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 902.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254431

CATALOG NUMBER: P3AS09R609035DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254431

CATALOG NUMBER: P3AS09R609035DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236341
5°	223112
10°	217297
15°	212351
20°	197440
25°	176502
30°	134806
35°	77845
40°	30199
45°	12590
50°	2763
55°	421
60°	307
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12590 cd/sqm

TEST NUMBER: P1254431

CATALOG NUMBER: P3AS09R609035DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.7	10.6
10°-20°	260.6	28.9
20°-30°	326.3	36.2
30°-40°	182.4	20.2
40°-50°	34.7	3.8
50°-60°	1.7	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.6	75.7
0°-40°	865.0	95.9
0°-60°	901.4	99.9
0°-90°	902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1078	
5°	1014	96
15°	935	261
25°	730	326
35°	291	182
45°	41	35
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1254431

CATALOG NUMBER: P3AS09R609035DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1077.8
1°	1073.4
2°	1059.3
3°	1042.7
4°	1027.2
5°	1013.6
6°	1003.2
7°	994.4
8°	987.8
9°	981.5
10°	975.9
11°	970.4
12°	964.1
13°	956.4
14°	947.2
15°	935.4
16°	921.0
17°	904.7
18°	886.3
19°	865.3
20°	846.1
21°	825.4
22°	804.0
23°	781.5
24°	756.8
25°	729.5
26°	697.4
27°	661.6
28°	621.4
29°	578.6
30°	532.4
31°	485.9
32°	438.0
32.5°	411.8
33°	388.2
34°	339.1
35°	290.8
36°	247.2
37°	201.1
37.5°	180.1
38°	159.4
39°	128.4
40°	105.5
42.5°	64.2
45°	40.6



TEST NUMBER: P1254431

CATALOG NUMBER: P3AS09R609035DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	22.5
50°	8.1
52.5°	1.8
55°	1.1
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)