

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255253

Luminaire Tested: P3AS17R659035DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1255253  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R659035DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1044.0 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255253  
CATALOG NUMBER: P3AS17R659035DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1255253  
 CATALOG NUMBER: P3AS17R659035DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	185775
5°	183293
10°	177129
15°	167061
20°	154083
25°	139871
30°	123892
35°	105417
40°	83871
45°	59200
50°	34387
55°	18771
60°	17455
65°	15825
70°	14426
75°	13471
80°	11744
85°	10064

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 59200 cd/sqm



TEST NUMBER: P1255253  
 CATALOG NUMBER: P3AS17R659035DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.3	7.5
10°-20°	205.9	19.7
20°-30°	264.6	25.3
30°-40°	244.8	23.4
40°-50°	147.7	14.2
50°-60°	50.4	4.8
60°-70°	30.3	2.9
70°-80°	17.1	1.6
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.8	52.6
0°-40°	793.5	76.0
0°-60°	991.7	95.0
0°-90°	1044.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1044.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	847	
5°	833	78
15°	736	206
25°	578	265
35°	394	245
45°	191	148
55°	49	50
65°	30	30
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1255253  
CATALOG NUMBER: P3AS17R659035DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	847.2
2.5°	843.3
5°	832.7
7.5°	816.7
10°	795.5
12.5°	769.0
15°	735.9
17.5°	700.1
20°	660.3
22.5°	619.2
25°	578.1
27.5°	534.3
30°	489.3
32.5°	444.2
35°	393.8
37.5°	344.7
40°	293.0
42.5°	241.3
45°	190.9
47.5°	144.5
50°	100.8
52.5°	63.6
55°	49.1
57.5°	43.8
60°	39.8
62.5°	34.5
65°	30.5
67.5°	26.5
70°	22.5
72.5°	19.9
75°	15.9
77.5°	13.3
80°	9.3
82.5°	6.6
85°	4.0
87.5°	2.7
90°	0.0

(END OF REPORT)