

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255278

Luminaire Tested: P3AS17R709035DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709035DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1333.9 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255278
CATALOG NUMBER: P3AS17R709035DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1255278
 CATALOG NUMBER: P3AS17R709035DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	258247
5°	255161
10°	247780
15°	237277
20°	222269
25°	201931
30°	174432
35°	139013
40°	101247
45°	66550
50°	31180
55°	9634
60°	9298
65°	8924
70°	8463
75°	8981
80°	8334
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 66550 cd/sqm



TEST NUMBER: P1255278
 CATALOG NUMBER: P3AS17R709035DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.2	8.2
10°-20°	292.5	21.9
20°-30°	380.2	28.5
30°-40°	322.6	24.2
40°-50°	166.3	12.5
50°-60°	32.0	2.4
60°-70°	17.4	1.3
70°-80°	10.6	0.8
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.9	58.6
0°-40°	1104.5	82.8
0°-60°	1302.9	97.7
0°-90°	1333.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1333.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1178	
5°	1159	109
15°	1045	293
25°	835	380
35°	519	323
45°	215	166
55°	25	32
65°	17	17
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P1255278
CATALOG NUMBER: P3AS17R709035DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1177.7
2.5°	1173.7
5°	1159.2
7.5°	1138.0
10°	1112.8
12.5°	1081.0
15°	1045.2
17.5°	1001.5
20°	952.5
22.5°	896.9
25°	834.6
27.5°	764.4
30°	688.9
32.5°	605.4
35°	519.3
37.5°	434.5
40°	353.7
42.5°	278.2
45°	214.6
47.5°	157.6
50°	91.4
52.5°	39.7
55°	25.2
57.5°	23.8
60°	21.2
62.5°	19.9
65°	17.2
67.5°	15.9
70°	13.2
72.5°	11.9
75°	10.6
77.5°	7.9
80°	6.6
82.5°	4.0
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)