

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254480

Luminaire Tested: P3AS09R709035DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709035DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 942.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254480
CATALOG NUMBER: P3AS09R709035DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1254480
 CATALOG NUMBER: P3AS09R709035DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187046
5°	178494
10°	169825
15°	165290
20°	159171
25°	150662
30°	140123
35°	117704
40°	75856
45°	35259
50°	9245
55°	2294
60°	2324
65°	1972
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35259 cd/sqm



TEST NUMBER: P1254480
 CATALOG NUMBER: P3AS09R709035DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	8.1
10°-20°	204.6	21.7
20°-30°	285.8	30.3
30°-40°	265.0	28.1
40°-50°	95.0	10.1
50°-60°	8.0	0.9
60°-70°	4.0	0.4
70°-80°	2.6	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.3	60.1
0°-40°	831.3	88.2
0°-60°	934.4	99.2
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	811	76
15°	728	205
25°	623	286
35°	440	265
45°	114	95
55°	6	8
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1254480
CATALOG NUMBER: P3AS09R709035DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	853.0
2.5°	840.2
5°	810.9
7.5°	783.8
10°	762.7
12.5°	745.4
15°	728.1
17.5°	707.0
20°	682.1
22.5°	653.5
25°	622.7
27.5°	591.0
30°	553.4
32.5°	505.2
35°	439.7
37.5°	356.1
40°	265.0
42.5°	180.7
45°	113.7
47.5°	63.2
50°	27.1
52.5°	9.0
55°	6.0
57.5°	5.3
60°	5.3
62.5°	4.5
65°	3.8
67.5°	3.8
70°	3.0
72.5°	3.0
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)