

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255308

Luminaire Tested: P3AS20R159035D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159035D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1373.0 lumens
Efficiency: N/A
Efficacy: 47.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255308
CATALOG NUMBER: P3AS20R159035D010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1255308
 CATALOG NUMBER: P3AS20R159035D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	346332
5°	336913
10°	307899
15°	269695
20°	231347
25°	193172
30°	154581
35°	115938
40°	84158
45°	55013
50°	34421
55°	23282
60°	20612
65°	18938
70°	17824
75°	16182
80°	15406
85°	13083

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55013 cd/sqm



TEST NUMBER: P1255308
 CATALOG NUMBER: P3AS20R159035D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.2	10.3
10°-20°	331.0	24.1
20°-30°	364.7	26.6
30°-40°	273.1	19.9
40°-50°	141.6	10.3
50°-60°	58.7	4.3
60°-70°	36.3	2.6
70°-80°	20.4	1.5
80°-90°	5.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.0	61.0
0°-40°	1110.1	80.9
0°-60°	1310.3	95.4
0°-90°	1373.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1373.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1579	
5°	1531	141
15°	1188	331
25°	798	365
35°	433	273
45°	177	142
55°	61	59
65°	36	36
75°	19	20
85°	5	6
90°	0	



TEST NUMBER: P1255308
CATALOG NUMBER: P3AS20R159035D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1579.4
1°	1581.1
2°	1575.9
3°	1565.4
4°	1549.8
5°	1530.6
6°	1506.3
7°	1480.2
8°	1448.9
9°	1415.9
10°	1382.8
12.5°	1287.1
15°	1188.0
17.5°	1088.8
20°	991.4
22.5°	892.3
25°	798.4
27.5°	704.4
30°	610.5
32.5°	518.3
35°	433.1
37.5°	360.1
40°	294.0
42.5°	233.1
45°	177.4
47.5°	133.9
50°	100.9
52.5°	74.8
55°	60.9
57.5°	53.9
60°	47.0
62.5°	41.7
65°	36.5
67.5°	31.3
70°	27.8
72.5°	22.6
75°	19.1
77.5°	15.7
80°	12.2
82.5°	8.7
85°	5.2
87.5°	1.7
90°	0.0

(END OF REPORT)