

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255326

Luminaire Tested: P3AS20R209035D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209035D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2181.1 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255326
CATALOG NUMBER: P3AS20R209035D010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1255326
 CATALOG NUMBER: P3AS20R209035D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3308397
5°	2785509
10°	1739803
15°	650446
20°	223273
25°	93054
30°	43830
35°	19622
40°	9275
45°	4745
50°	1740
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4745 cd/sqm



TEST NUMBER: P1255326
 CATALOG NUMBER: P3AS20R209035D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1052.3	48.2
10°-20°	866.8	39.7
20°-30°	197.0	9.0
30°-40°	50.1	2.3
40°-50°	12.6	0.6
50°-60°	1.6	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2116.2	97.0
0°-40°	2166.3	99.3
0°-60°	2180.5	100.0
0°-90°	2181.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2181.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15088	
5°	12655	###
15°	2865	867
25°	385	197
35°	73	50
45°	15	13
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1255326
CATALOG NUMBER: P3AS20R209035D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	15087.5
1°	14959.6
2°	14582.7
3°	14042.1
4°	13378.6
5°	12654.6
6°	11848.0
7°	10957.7
8°	9919.1
9°	8889.8
10°	7813.6
11°	6668.4
12°	5524.9
13°	4556.2
14°	3630.1
15°	2865.2
16°	2261.5
17°	1783.9
18°	1433.5
19°	1165.7
20°	956.8
21°	799.9
22°	667.7
23°	555.1
24°	463.0
25°	384.6
27.5°	251.6
30°	173.1
32.5°	106.6
35°	73.3
37.5°	46.9
40°	32.4
42.5°	22.2
45°	15.3
47.5°	10.2
50°	5.1
52.5°	2.6
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1255326
CATALOG NUMBER: P3AS20R209035D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)