

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254654

Luminaire Tested: P3AS13R259035DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259035DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 803.0 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254654
CATALOG NUMBER: P3AS13R259035DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1254654
 CATALOG NUMBER: P3AS13R259035DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55	55	55	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50	50	50	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47	47	47	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209523
5°	198877
10°	172252
15°	140228
20°	110820
25°	88360
30°	71631
35°	58330
40°	48348
45°	40717
50°	34455
55°	30355
60°	26577
65°	23193
70°	20388
75°	17114
80°	12754
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 40717 cd/sqm



TEST NUMBER: P1254654

CATALOG NUMBER: P3AS13R259035DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.0	10.2
10°-20°	171.3	21.3
20°-30°	168.8	21.0
30°-40°	137.5	17.1
40°-50°	102.0	12.7
50°-60°	71.2	8.9
60°-70°	44.6	5.6
70°-80°	21.5	2.7
80°-90°	4.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.2	52.6
0°-40°	559.6	69.7
0°-60°	732.8	91.3
0°-90°	803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	956	
5°	904	82
15°	618	171
25°	365	169
35°	218	137
45°	131	102
55°	79	71
65°	45	45
75°	20	21
85°	3	4
90°	0	



TEST NUMBER: P1254654
CATALOG NUMBER: P3AS13R259035DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	955.5
2.5°	942.5
5°	903.5
7.5°	844.3
10°	773.6
12.5°	695.7
15°	617.7
17.5°	541.2
20°	474.9
22.5°	417.1
25°	365.2
27.5°	320.4
30°	282.9
32.5°	248.3
35°	217.9
37.5°	192.0
40°	168.9
42.5°	148.7
45°	131.3
47.5°	115.5
50°	101.0
52.5°	89.5
55°	79.4
57.5°	69.3
60°	60.6
62.5°	52.0
65°	44.7
67.5°	37.5
70°	31.8
72.5°	26.0
75°	20.2
77.5°	14.4
80°	10.1
82.5°	5.8
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)