

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255445

Luminaire Tested: P3AS20R409035D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409035D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2442.9 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255445
CATALOG NUMBER: P3AS20R409035D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P125445
 CATALOG NUMBER: P3AS20R409035D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85		
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82		
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79		
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76		
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73		
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1286300
5°	1280120
10°	1238387
15°	1095648
20°	714855
25°	253224
30°	53704
35°	17694
40°	6469
45°	2171
50°	1774
55°	1988
60°	1535
65°	1816
70°	1090
75°	1440
80°	2147
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 2856 cd/sqm



TEST NUMBER: P1255445
 CATALOG NUMBER: P3AS20R409035D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.2	22.4
10°-20°	1274.3	52.2
20°-30°	553.0	22.6
30°-40°	51.0	2.1
40°-50°	7.2	0.3
50°-60°	4.5	0.2
60°-70°	3.2	0.1
70°-80°	1.8	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2374.5	97.2
0°-40°	2425.5	99.3
0°-60°	2437.2	99.8
0°-90°	2442.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2442.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5866	
5°	5816	547
15°	4826	1274
25°	1047	553
35°	66	51
45°	7	7
55°	5	4
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1255445
CATALOG NUMBER: P3AS20R409035D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5866.0
2.5°	5859.0
5°	5815.6
7.5°	5723.4
10°	5561.7
12.5°	5288.8
15°	4826.3
17.5°	4059.6
20°	3063.4
22.5°	1988.9
25°	1046.6
27.5°	450.3
30°	212.1
32.5°	114.7
35°	66.1
37.5°	40.0
40°	22.6
42.5°	12.2
45°	7.0
47.5°	5.2
50°	5.2
52.5°	5.2
55°	5.2
57.5°	5.2
60°	3.5
62.5°	3.5
65°	3.5
67.5°	3.5
70°	1.7
72.5°	1.7
75°	1.7
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)