

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255448

Luminaire Tested: P3AS20R409035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 993.1 lumens
Efficiency: N/A
Efficacy: 34.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255448
CATALOG NUMBER: P3AS20R409035D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1255448

CATALOG NUMBER: P3AS20R409035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439395
5°	426633
10°	387145
15°	319843
20°	230717
25°	142702
30°	77252
35°	39940
40°	21726
45°	12156
50°	6106
55°	4549
60°	4122
65°	3995
70°	3847
75°	3643
80°	3283
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12156 cd/sqm



TEST NUMBER: P1255448
 CATALOG NUMBER: P3AS20R409035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.7	18.0
10°-20°	383.6	38.6
20°-30°	273.8	27.6
30°-40°	100.8	10.1
40°-50°	31.7	3.2
50°-60°	11.0	1.1
60°-70°	7.6	0.8
70°-80°	4.5	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	836.1	84.2
0°-40°	936.9	94.3
0°-60°	979.6	98.6
0°-90°	993.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	993.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2004	
5°	1938	179
15°	1409	384
25°	590	274
35°	149	101
45°	39	32
55°	12	11
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1255448
CATALOG NUMBER: P3AS20R409035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2003.8
2.5°	1988.5
5°	1938.2
7.5°	1854.6
10°	1738.7
12.5°	1591.3
15°	1408.9
17.5°	1204.3
20°	988.7
22.5°	776.5
25°	589.8
27.5°	433.0
30°	305.1
32.5°	213.9
35°	149.2
37.5°	105.7
40°	75.9
42.5°	54.5
45°	39.2
47.5°	26.4
50°	17.9
52.5°	12.8
55°	11.9
57.5°	11.1
60°	9.4
62.5°	8.5
65°	7.7
67.5°	6.8
70°	6.0
72.5°	5.1
75°	4.3
77.5°	3.4
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)