

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255463

Luminaire Tested: P3AS20R409035D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409035D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1278.0 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255463
CATALOG NUMBER: P3AS20R409035D010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1255463

CATALOG NUMBER: P3AS20R409035D010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	397929
5°	389896
10°	363008
15°	316392
20°	254986
25°	191116
30°	134375
35°	88017
40°	53300
45°	31848
50°	19002
55°	15292
60°	13727
65°	11726
70°	11156
75°	8811
80°	8840
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31848 cd/sqm



TEST NUMBER: P1255463
 CATALOG NUMBER: P3AS20R409035D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.5	12.9
10°-20°	383.9	30.0
20°-30°	361.7	28.3
30°-40°	209.2	16.4
40°-50°	83.4	6.5
50°-60°	36.9	2.9
60°-70°	22.8	1.8
70°-80°	11.9	0.9
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.1	71.2
0°-40°	1119.3	87.6
0°-60°	1239.5	97.0
0°-90°	1278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1815	
5°	1771	164
15°	1394	384
25°	790	362
35°	329	209
45°	103	83
55°	40	37
65°	23	23
75°	10	12
85°	4	4
90°	0	



TEST NUMBER: P1255463
CATALOG NUMBER: P3AS20R409035D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1814.7
2.5°	1804.3
5°	1771.3
7.5°	1710.4
10°	1630.3
12.5°	1522.4
15°	1393.7
17.5°	1249.3
20°	1092.7
22.5°	936.1
25°	789.9
27.5°	654.2
30°	530.7
32.5°	422.8
35°	328.8
37.5°	248.8
40°	186.2
42.5°	139.2
45°	102.7
47.5°	74.8
50°	55.7
52.5°	45.2
55°	40.0
57.5°	36.5
60°	31.3
62.5°	26.1
65°	22.6
67.5°	19.1
70°	17.4
72.5°	13.9
75°	10.4
77.5°	8.7
80°	7.0
82.5°	5.2
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)