

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254709

Luminaire Tested: P3AS13R359035DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359035DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 649.0 lumens
Efficiency: N/A
Efficacy: 44.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254709

CATALOG NUMBER: P3AS13R359035DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1254709

CATALOG NUMBER: P3AS13R359035DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208602
5°	203455
10°	186013
15°	157890
20°	124984
25°	94530
30°	68821
35°	46552
40°	28596
45°	16436
50°	9893
55°	8028
60°	7017
65°	6226
70°	5129
75°	5083
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16436 cd/sqm

TEST NUMBER: P1254709

CATALOG NUMBER: P3AS13R359035DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.4	13.2
10°-20°	191.7	29.5
20°-30°	179.4	27.6
30°-40°	109.8	16.9
40°-50°	43.3	6.7
50°-60°	19.1	2.9
60°-70°	11.9	1.8
70°-80°	6.3	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.5	70.3
0°-40°	566.3	87.3
0°-60°	628.7	96.9
0°-90°	649.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	951	
5°	924	85
15°	696	192
25°	391	179
35°	174	110
45°	53	43
55°	21	19
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1254709

CATALOG NUMBER: P3AS13R359035DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	951.3
1°	952.3
2°	949.3
3°	943.3
4°	934.3
5°	924.3
6°	911.3
7°	896.4
8°	878.4
9°	858.4
10°	835.4
11°	811.4
12°	785.4
13°	757.5
14°	726.5
15°	695.5
17.5°	615.6
20°	535.6
22.5°	458.7
25°	390.7
27.5°	327.8
30°	271.8
32.5°	219.8
35°	173.9
37.5°	132.9
40°	99.9
42.5°	71.9
45°	53.0
47.5°	38.0
50°	29.0
52.5°	24.0
55°	21.0
57.5°	18.0
60°	16.0
62.5°	14.0
65°	12.0
67.5°	10.0
70°	8.0
72.5°	7.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0



TEST NUMBER: P1254709

CATALOG NUMBER: P3AS13R359035DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)