

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255465

Luminaire Tested: P3AS20R409035D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409035D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1278.0 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255465

CATALOG NUMBER: P3AS20R409035D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255465

CATALOG NUMBER: P3AS20R409035D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	397929
5°	389896
10°	363008
15°	316392
20°	254986
25°	191116
30°	134375
35°	88017
40°	53300
45°	31848
50°	19002
55°	15292
60°	13727
65°	11726
70°	11156
75°	8811
80°	8840
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31848 cd/sqm

TEST NUMBER: P1255465

CATALOG NUMBER: P3AS20R409035D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.5	12.9
10°-20°	383.9	30.0
20°-30°	361.7	28.3
30°-40°	209.2	16.4
40°-50°	83.4	6.5
50°-60°	36.9	2.9
60°-70°	22.8	1.8
70°-80°	11.9	0.9
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.1	71.2
0°-40°	1119.3	87.6
0°-60°	1239.5	97.0
0°-90°	1278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1815	
5°	1771	164
15°	1394	384
25°	790	362
35°	329	209
45°	103	83
55°	40	37
65°	23	23
75°	10	12
85°	4	4
90°	0	

TEST NUMBER: P1255465

CATALOG NUMBER: P3AS20R409035D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1814.7
2.5°	1804.3
5°	1771.3
7.5°	1710.4
10°	1630.3
12.5°	1522.4
15°	1393.7
17.5°	1249.3
20°	1092.7
22.5°	936.1
25°	789.9
27.5°	654.2
30°	530.7
32.5°	422.8
35°	328.8
37.5°	248.8
40°	186.2
42.5°	139.2
45°	102.7
47.5°	74.8
50°	55.7
52.5°	45.2
55°	40.0
57.5°	36.5
60°	31.3
62.5°	26.1
65°	22.6
67.5°	19.1
70°	17.4
72.5°	13.9
75°	10.4
77.5°	8.7
80°	7.0
82.5°	5.2
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)