

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254742

Luminaire Tested: P3AS13R409035DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409035DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 735.0 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254742
CATALOG NUMBER: P3AS13R409035DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1254742
 CATALOG NUMBER: P3AS13R409035DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228863
5°	224235
10°	208769
15°	181953
20°	146639
25°	109918
30°	77278
35°	50621
40°	30657
45°	18296
50°	10916
55°	8793
60°	7894
65°	6745
70°	6411
75°	5083
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18296 cd/sqm



TEST NUMBER: P1254742
 CATALOG NUMBER: P3AS13R409035DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	12.9
10°-20°	220.8	30.0
20°-30°	208.0	28.3
30°-40°	120.3	16.4
40°-50°	47.9	6.5
50°-60°	21.2	2.9
60°-70°	13.1	1.8
70°-80°	6.9	0.9
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.4	71.2
0°-40°	643.7	87.6
0°-60°	712.9	97.0
0°-90°	735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1044	
5°	1019	95
15°	802	221
25°	454	208
35°	189	120
45°	59	48
55°	23	21
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1254742
CATALOG NUMBER: P3AS13R409035DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1043.7
2.5°	1037.7
5°	1018.7
7.5°	983.7
10°	937.6
12.5°	875.6
15°	801.5
17.5°	718.5
20°	628.4
22.5°	538.4
25°	454.3
27.5°	376.3
30°	305.2
32.5°	243.2
35°	189.1
37.5°	143.1
40°	107.1
42.5°	80.1
45°	59.0
47.5°	43.0
50°	32.0
52.5°	26.0
55°	23.0
57.5°	21.0
60°	18.0
62.5°	15.0
65°	13.0
67.5°	11.0
70°	10.0
72.5°	8.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)