

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254776

Luminaire Tested: P3AS13R509035DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509035DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1389.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254776
CATALOG NUMBER: P3AS13R509035DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1254776
 CATALOG NUMBER: P3AS13R509035DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485400
5°	472484
10°	450871
15°	408175
20°	353134
25°	289662
30°	166405
35°	51691
40°	13883
45°	4869
50°	1160
55°	382
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4869 cd/sqm



TEST NUMBER: P1254776
 CATALOG NUMBER: P3AS13R509035DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.0	14.5
10°-20°	498.2	35.9
20°-30°	523.6	37.7
30°-40°	149.9	10.8
40°-50°	14.6	1.1
50°-60°	1.2	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1222.9	88.0
0°-40°	1372.7	98.8
0°-60°	1388.6	100.0
0°-90°	1389.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1389.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2214	
5°	2146	201
15°	1798	498
25°	1197	524
35°	193	150
45°	16	15
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1254776
CATALOG NUMBER: P3AS13R509035DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2213.6
1°	2210.2
2°	2200.4
3°	2186.2
4°	2167.0
5°	2146.5
6°	2124.4
7°	2100.9
8°	2078.8
9°	2053.4
10°	2024.9
11°	1992.1
12°	1954.4
13°	1907.3
14°	1856.3
15°	1798.0
16°	1736.3
17°	1676.5
18°	1615.2
19°	1561.3
20°	1513.3
21°	1467.2
22°	1414.8
23°	1354.5
24°	1284.0
25°	1197.2
26°	1103.1
27°	998.3
28°	893.9
29°	781.2
30°	657.2
31°	541.0
32°	434.2
32.5°	387.6
33°	340.6
34°	261.2
35°	193.1
36°	141.6
37°	105.4
37.5°	91.2
38°	78.9
39°	61.3
40°	48.5
42.5°	27.4
45°	15.7



TEST NUMBER: P1254776
CATALOG NUMBER: P3AS13R509035DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.8
50°	3.4
52.5°	1.5
55°	1.0
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)