

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255502

Luminaire Tested: P3AS20R509035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 959.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255502
CATALOG NUMBER: P3AS20R509035D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1255502
 CATALOG NUMBER: P3AS20R509035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76			76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67			67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64			64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60			60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57			57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	305326
5°	299185
10°	280222
15°	250875
20°	211115
25°	161114
30°	104700
35°	62078
40°	35867
45°	17986
50°	6686
55°	5199
60°	4868
65°	4410
70°	4360
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17986 cd/sqm



TEST NUMBER: P1255502
 CATALOG NUMBER: P3AS20R509035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	13.2
10°-20°	305.6	31.9
20°-30°	299.8	31.3
30°-40°	151.0	15.7
40°-50°	47.7	5.0
50°-60°	12.4	1.3
60°-70°	8.7	0.9
70°-80°	5.4	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	731.9	76.3
0°-40°	882.9	92.1
0°-60°	943.0	98.3
0°-90°	959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1392	
5°	1359	126
15°	1105	306
25°	666	300
35°	232	151
45°	58	48
55°	14	12
65°	8	9
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1255502
CATALOG NUMBER: P3AS20R509035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1392.4
2.5°	1383.9
5°	1359.2
7.5°	1314.8
10°	1258.5
12.5°	1186.1
15°	1105.1
17.5°	1011.3
20°	904.7
22.5°	789.6
25°	665.9
27.5°	534.6
30°	413.5
32.5°	311.2
35°	231.9
37.5°	171.4
40°	125.3
42.5°	88.7
45°	58.0
47.5°	33.3
50°	19.6
52.5°	14.5
55°	13.6
57.5°	11.9
60°	11.1
62.5°	10.2
65°	8.5
67.5°	7.7
70°	6.8
72.5°	6.0
75°	5.1
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)