

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255508

Luminaire Tested: P3AS20R509035D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509035D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 747.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255508

CATALOG NUMBER: P3AS20R509035D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255508

CATALOG NUMBER: P3AS20R509035D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151808
5°	149570
10°	142950
15°	132396
20°	118964
25°	104595
30°	88950
35°	72116
40°	54187
45°	34887
50°	16579
55°	13037
60°	12324
65°	11519
70°	10386
75°	9404
80°	8587
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34887 cd/sqm

TEST NUMBER: P1255508

CATALOG NUMBER: P3AS20R509035D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	8.5
10°-20°	162.6	21.8
20°-30°	197.5	26.4
30°-40°	167.5	22.4
40°-50°	87.0	11.6
50°-60°	31.4	4.2
60°-70°	21.7	2.9
70°-80°	11.8	1.6
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	56.7
0°-40°	591.3	79.2
0°-60°	709.8	95.0
0°-90°	747.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	747.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	692	
5°	680	64
15°	583	163
25°	432	198
35°	269	168
45°	112	87
55°	34	31
65°	22	22
75°	11	12
85°	3	4
90°	0	

TEST NUMBER: P1255508

CATALOG NUMBER: P3AS20R509035D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	692.3
2.5°	689.7
5°	679.5
7.5°	664.1
10°	642.0
12.5°	613.8
15°	583.2
17.5°	548.2
20°	509.8
22.5°	470.6
25°	432.3
27.5°	392.2
30°	351.3
32.5°	310.3
35°	269.4
37.5°	229.3
40°	189.3
42.5°	150.9
45°	112.5
47.5°	75.0
50°	48.6
52.5°	37.5
55°	34.1
57.5°	30.7
60°	28.1
62.5°	24.7
65°	22.2
67.5°	18.8
70°	16.2
72.5°	13.6
75°	11.1
77.5°	8.5
80°	6.8
82.5°	5.1
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)