

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254822

Luminaire Tested: P3AS13R559035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 24.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254822

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254822

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97119
5°	94673
10°	88019
15°	78389
20°	66599
25°	53761
30°	40994
35°	29152
40°	19236
45°	11412
50°	6686
55°	4129
60°	3640
65°	3321
70°	2821
75°	2457
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1254822

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.9	11.2
10°-20°	95.7	26.8
20°-30°	101.4	28.4
30°-40°	68.5	19.2
40°-50°	30.0	8.4
50°-60°	10.7	3.0
60°-70°	6.3	1.8
70°-80°	3.3	0.9
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.1	66.4
0°-40°	305.6	85.6
0°-60°	346.3	97.0
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	443	
5°	430	40
15°	345	96
25°	222	101
35°	109	69
45°	37	30
55°	11	11
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254822

CATALOG NUMBER: P3AS13R559035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	442.9
2.5°	439.4
5°	430.1
7.5°	414.9
10°	395.3
12.5°	371.8
15°	345.3
17.5°	315.9
20°	285.4
22.5°	253.6
25°	222.2
27.5°	191.3
30°	161.9
32.5°	133.9
35°	108.9
37.5°	86.3
40°	67.2
42.5°	50.5
45°	36.8
47.5°	27.0
50°	19.6
52.5°	13.7
55°	10.8
57.5°	9.8
60°	8.3
62.5°	7.4
65°	6.4
67.5°	5.4
70°	4.4
72.5°	3.9
75°	2.9
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)