

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255553

Luminaire Tested: P3AS20R609035D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609035D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2249.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P125553
CATALOG NUMBER: P3AS20R609035D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1255553
 CATALOG NUMBER: P3AS20R609035D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81	81	81	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71	71	71	71
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66	66	66	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	63	59	58	58	58	58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55	55	55	55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	537040
5°	515737
10°	531008
15°	537824
20°	474898
25°	400233
30°	324607
35°	211397
40°	97096
45°	37213
50°	12452
55°	3326
60°	3070
65°	2698
70°	2244
75°	2965
80°	2147
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37213 cd/sqm



TEST NUMBER: P1255553
 CATALOG NUMBER: P3AS20R609035D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.5	10.0
10°-20°	648.8	28.8
20°-30°	756.7	33.6
30°-40°	488.3	21.7
40°-50°	109.4	4.9
50°-60°	10.9	0.5
60°-70°	5.2	0.2
70°-80°	3.0	0.1
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.0	72.5
0°-40°	2119.3	94.2
0°-60°	2239.7	99.6
0°-90°	2249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2449	
5°	2343	226
15°	2369	649
25°	1654	757
35°	790	488
45°	120	109
55°	9	11
65°	5	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P1255553
CATALOG NUMBER: P3AS20R609035D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2449.1
2.5°	2409.1
5°	2343.0
7.5°	2339.6
10°	2384.8
12.5°	2414.3
15°	2369.1
17.5°	2233.4
20°	2035.1
22.5°	1828.2
25°	1654.2
27.5°	1483.7
30°	1282.0
32.5°	1045.4
35°	789.7
37.5°	539.2
40°	339.2
42.5°	203.5
45°	120.0
47.5°	69.6
50°	36.5
52.5°	12.2
55°	8.7
57.5°	7.0
60°	7.0
62.5°	5.2
65°	5.2
67.5°	5.2
70°	3.5
72.5°	3.5
75°	3.5
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)