

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254845

Luminaire Tested: P3AS13R609035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 404.0 lumens
Efficiency: N/A
Efficacy: 27.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254845
CATALOG NUMBER: P3AS13R609035DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1254845
 CATALOG NUMBER: P3AS13R609035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82				82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44				44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71727
5°	70900
10°	68447
15°	64677
20°	59622
25°	53979
30°	47931
35°	40957
40°	32575
45°	22948
50°	13714
55°	6920
60°	6666
65°	6123
70°	5642
75°	5422
80°	4925
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22948 cd/sqm



TEST NUMBER: P1254845
 CATALOG NUMBER: P3AS13R609035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	7.5
10°-20°	79.6	19.7
20°-30°	102.2	25.3
30°-40°	94.8	23.5
40°-50°	57.7	14.3
50°-60°	19.2	4.8
60°-70°	11.7	2.9
70°-80°	6.6	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.1	52.5
0°-40°	306.9	76.0
0°-60°	383.9	95.0
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	327	
5°	322	30
15°	285	80
25°	223	102
35°	153	95
45°	74	58
55°	18	19
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1254845
CATALOG NUMBER: P3AS13R609035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	327.1
2.5°	325.6
5°	322.1
7.5°	315.8
10°	307.4
12.5°	297.1
15°	284.9
17.5°	270.7
20°	255.5
22.5°	239.3
25°	223.1
27.5°	206.4
30°	189.3
32.5°	172.1
35°	153.0
37.5°	132.9
40°	113.8
42.5°	93.7
45°	74.0
47.5°	57.4
50°	40.2
52.5°	24.0
55°	18.1
57.5°	16.7
60°	15.2
62.5°	13.2
65°	11.8
67.5°	10.3
70°	8.8
72.5°	7.4
75°	6.4
77.5°	4.9
80°	3.9
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)