

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254879

Luminaire Tested: P3AS13R659035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 788.0 lumens
Efficiency: N/A
Efficacy: 54.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254879

CATALOG NUMBER: P3AS13R659035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254879

CATALOG NUMBER: P3AS13R659035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140230
5°	138344
10°	133709
15°	126085
20°	116303
25°	105563
30°	93508
35°	79558
40°	63319
45°	44687
50°	25961
55°	14145
60°	13157
65°	11934
70°	10899
75°	10167
80°	8840
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44687 cd/sqm

TEST NUMBER: P1254879

CATALOG NUMBER: P3AS13R659035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	7.5
10°-20°	155.4	19.7
20°-30°	199.7	25.3
30°-40°	184.7	23.4
40°-50°	111.5	14.2
50°-60°	38.0	4.8
60°-70°	22.9	2.9
70°-80°	12.9	1.6
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.2	52.6
0°-40°	598.9	76.0
0°-60°	748.5	95.0
0°-90°	788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	640	
5°	628	59
15°	555	155
25°	436	200
35°	297	185
45°	144	112
55°	37	38
65°	23	23
75°	12	13
85°	3	4
90°	0	

TEST NUMBER: P1254879

CATALOG NUMBER: P3AS13R659035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	639.5
2.5°	636.5
5°	628.5
7.5°	616.5
10°	600.5
12.5°	580.4
15°	555.4
17.5°	528.4
20°	498.4
22.5°	467.4
25°	436.3
27.5°	403.3
30°	369.3
32.5°	335.3
35°	297.2
37.5°	260.2
40°	221.2
42.5°	182.1
45°	144.1
47.5°	109.1
50°	76.1
52.5°	48.0
55°	37.0
57.5°	33.0
60°	30.0
62.5°	26.0
65°	23.0
67.5°	20.0
70°	17.0
72.5°	15.0
75°	12.0
77.5°	10.0
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

(END OF REPORT)