

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254884

Luminaire Tested: P3AS13R659035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1003.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254884

CATALOG NUMBER: P3AS13R659035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254884

CATALOG NUMBER: P3AS13R659035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236538
5°	233700
10°	224823
15°	210603
20°	189436
25°	160848
30°	125817
35°	89650
40°	58653
45°	36283
50°	18422
55°	6499
60°	5701
65°	5707
70°	5129
75°	5083
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36283 cd/sqm

TEST NUMBER: P1254884

CATALOG NUMBER: P3AS13R659035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.7	9.9
10°-20°	258.2	25.7
20°-30°	301.7	30.1
30°-40°	210.9	21.0
40°-50°	92.8	9.3
50°-60°	20.7	2.1
60°-70°	10.5	1.0
70°-80°	6.3	0.6
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.6	65.8
0°-40°	870.5	86.8
0°-60°	984.0	98.1
0°-90°	1003.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1003.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1079	
5°	1062	100
15°	928	258
25°	665	302
35°	335	211
45°	117	93
55°	17	21
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1254884

CATALOG NUMBER: P3AS13R659035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1078.7
2.5°	1074.7
5°	1061.7
7.5°	1039.7
10°	1009.7
12.5°	972.7
15°	927.7
17.5°	872.8
20°	811.8
22.5°	742.8
25°	664.8
27.5°	582.8
30°	496.9
32.5°	413.9
35°	334.9
37.5°	265.9
40°	204.9
42.5°	155.0
45°	117.0
47.5°	86.0
50°	54.0
52.5°	28.0
55°	17.0
57.5°	15.0
60°	13.0
62.5°	12.0
65°	11.0
67.5°	9.0
70°	8.0
72.5°	7.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)