

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254890

Luminaire Tested: P3AS13R709035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1251.0 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254890

CATALOG NUMBER: P3AS13R709035DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1254890

CATALOG NUMBER: P3AS13R709035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248423
5°	237045
10°	225536
15°	219502
20°	211395
25°	200068
30°	186079
35°	156306
40°	100760
45°	46827
50°	12281
55°	3058
60°	3070
65°	2594
70°	2565
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46827 cd/sqm

TEST NUMBER: P1254890

CATALOG NUMBER: P3AS13R709035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	8.1
10°-20°	271.7	21.7
20°-30°	379.6	30.3
30°-40°	351.9	28.1
40°-50°	126.2	10.1
50°-60°	10.7	0.9
60°-70°	5.3	0.4
70°-80°	3.4	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.1	60.1
0°-40°	1104.0	88.2
0°-60°	1240.9	99.2
0°-90°	1251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1133	
5°	1077	101
15°	967	272
25°	827	380
35°	584	352
45°	151	126
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254890

CATALOG NUMBER: P3AS13R709035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1132.9
2.5°	1115.9
5°	1076.9
7.5°	1040.9
10°	1012.9
12.5°	989.9
15°	966.9
17.5°	938.9
20°	905.9
22.5°	867.9
25°	826.9
27.5°	784.9
30°	734.9
32.5°	670.9
35°	583.9
37.5°	472.9
40°	352.0
42.5°	240.0
45°	151.0
47.5°	84.0
50°	36.0
52.5°	12.0
55°	8.0
57.5°	7.0
60°	7.0
62.5°	6.0
65°	5.0
67.5°	5.0
70°	4.0
72.5°	4.0
75°	3.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)