

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255639

Luminaire Tested: P3AS24R159035D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159035D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2638.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255639

CATALOG NUMBER: P3AS24R159035D010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1255639

CATALOG NUMBER: P3AS24R159035D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98			
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96			
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94			
4	107	102	99	96	106	101	98	96	99	97	95	98	96	94	96	94	93	92			
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90			
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88			
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87			
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85			
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	89	86	85	84			
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5023435
5°	4096269
10°	2006108
15°	614033
20°	260026
25°	117612
30°	45855
35°	21148
40°	6584
45°	2481
50°	1023
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2481 cd/sqm

TEST NUMBER: P1255639

CATALOG NUMBER: P3AS24R159035D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1448.5	54.9
10°-20°	888.8	33.7
20°-30°	238.7	9.1
30°-40°	52.6	2.0
40°-50°	7.4	0.3
50°-60°	1.3	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2576.1	97.7
0°-40°	2628.7	99.6
0°-60°	2637.4	100.0
0°-90°	2638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2638.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22909	
5°	18609	###
15°	2705	889
25°	486	239
35°	79	53
45°	8	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1255639

CATALOG NUMBER: P3AS24R159035D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	22908.7
1°	22765.6
2°	22306.5
3°	21479.3
4°	20233.9
5°	18609.4
6°	16771.9
7°	14725.3
8°	12844.8
9°	10851.2
10°	9009.6
11°	7187.1
12°	5529.6
13°	4253.2
14°	3367.0
15°	2704.8
17.5°	1676.5
20°	1114.3
22.5°	750.2
25°	486.1
27.5°	288.1
30°	181.1
32.5°	122.0
35°	79.0
37.5°	44.0
40°	23.0
42.5°	13.0
45°	8.0
47.5°	5.0
50°	3.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1255639
CATALOG NUMBER: P3AS24R159035D010 E3D1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)