

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254908

Luminaire Tested: P3AS13R709035DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709035DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 719.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254908

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1254908

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168649
5°	165551
10°	156109
15°	141681
20°	123934
25°	104546
30°	85583
35°	66388
40°	47518
45°	30081
50°	15010
55°	9175
60°	7894
65°	7264
70°	6411
75°	5931
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30081 cd/sqm

TEST NUMBER: P1254908

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	9.8
10°-20°	173.7	24.2
20°-30°	197.8	27.5
30°-40°	154.6	21.5
40°-50°	76.0	10.6
50°-60°	23.4	3.2
60°-70°	13.8	1.9
70°-80°	7.4	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.6	61.4
0°-40°	596.3	82.9
0°-60°	695.6	96.7
0°-90°	719.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	719.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	769	
5°	752	70
15°	624	174
25°	432	198
35°	248	155
45°	97	76
55°	24	23
65°	14	14
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1254908

CATALOG NUMBER: P3AS13R709035DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	769.1
2.5°	765.1
5°	752.1
7.5°	731.1
10°	701.1
12.5°	666.1
15°	624.1
17.5°	579.1
20°	531.1
22.5°	481.1
25°	432.1
27.5°	384.1
30°	338.0
32.5°	292.0
35°	248.0
37.5°	206.0
40°	166.0
42.5°	129.0
45°	97.0
47.5°	68.0
50°	44.0
52.5°	29.0
55°	24.0
57.5°	21.0
60°	18.0
62.5°	16.0
65°	14.0
67.5°	12.0
70°	10.0
72.5°	8.0
75°	7.0
77.5°	6.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)