

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254972

Luminaire Tested: P3AS17R159035DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159035DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 873.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254972
CATALOG NUMBER: P3AS17R159035DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1254972
 CATALOG NUMBER: P3AS17R159035DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72	72	72	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55	55	55	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254037
5°	238146
10°	195276
15°	151715
20°	119757
25°	95449
30°	76619
35°	62533
40°	51525
45°	43353
50°	37253
55°	32228
60°	28550
65°	24854
70°	22119
75°	17877
80°	14522
85°	9561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43353 cd/sqm



TEST NUMBER: P1254972
 CATALOG NUMBER: P3AS17R159035DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	11.1
10°-20°	187.2	21.4
20°-30°	182.0	20.8
30°-40°	147.1	16.8
40°-50°	109.2	12.5
50°-60°	76.3	8.7
60°-70°	47.8	5.5
70°-80°	22.7	2.6
80°-90°	4.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.8	53.4
0°-40°	612.9	70.2
0°-60°	798.3	91.4
0°-90°	873.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1158	
5°	1082	97
15°	668	187
25°	394	182
35°	234	147
45°	140	109
55°	84	76
65°	48	48
75°	21	23
85°	4	4
90°	0	

TEST NUMBER: P1254972
CATALOG NUMBER: P3AS17R159035DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1158.5
2.5°	1139.4
5°	1081.9
7.5°	990.0
10°	877.0
12.5°	766.0
15°	668.3
17.5°	586.0
20°	513.2
22.5°	450.0
25°	394.5
27.5°	344.7
30°	302.6
32.5°	266.2
35°	233.6
37.5°	204.9
40°	180.0
42.5°	158.9
45°	139.8
47.5°	124.5
50°	109.2
52.5°	95.7
55°	84.3
57.5°	74.7
60°	65.1
62.5°	55.5
65°	47.9
67.5°	40.2
70°	34.5
72.5°	26.8
75°	21.1
77.5°	15.3
80°	11.5
82.5°	5.7
85°	3.8
87.5°	0.0
90°	0.0

(END OF REPORT)