

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255732

Luminaire Tested: P3AS24R309035D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309035D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2576.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255732
CATALOG NUMBER: P3AS24R309035D010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1255732
 CATALOG NUMBER: P3AS24R309035D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	93	92	90
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	93	91	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	90	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	88	85	83	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	86	83	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	84	81	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	82	79	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	80	77	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2049551
5°	2022821
10°	1766100
15°	1122549
20°	444749
25°	148557
30°	69125
35°	31320
40°	12023
45°	5892
50°	1706
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5892 cd/sqm



TEST NUMBER: P1255732
 CATALOG NUMBER: P3AS24R309035D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	840.2	32.6
10°-20°	1302.9	50.6
20°-30°	336.0	13.0
30°-40°	78.9	3.1
40°-50°	15.4	0.6
50°-60°	1.8	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2479.1	96.2
0°-40°	2558.0	99.3
0°-60°	2575.1	100.0
0°-90°	2576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2576.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9347	
5°	9190	840
15°	4945	1303
25°	614	336
35°	117	79
45°	19	15
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1255732
CATALOG NUMBER: P3AS24R309035D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	9346.7
1°	9339.7
2°	9317.7
3°	9292.7
4°	9255.7
5°	9189.7
6°	9082.7
7°	8904.7
8°	8661.7
9°	8344.7
10°	7931.7
11°	7440.7
12°	6904.8
13°	6287.8
14°	5641.8
15°	4944.8
16°	4261.9
17°	3603.9
18°	2972.9
19°	2393.9
20°	1905.9
21°	1499.9
22°	1180.0
23°	934.0
24°	748.0
25°	614.0
26°	512.0
27°	435.0
28°	376.0
29°	322.0
30°	273.0
32.5°	172.0
35°	117.0
37.5°	73.0
40°	42.0
42.5°	28.0
45°	19.0
47.5°	11.0
50°	5.0
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0



TEST NUMBER: P1255732
CATALOG NUMBER: P3AS24R309035D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)