

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255021

Luminaire Tested: P3AS17R259035DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259035DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.0 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255021
CATALOG NUMBER: P3AS17R259035DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1255021
 CATALOG NUMBER: P3AS17R259035DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252874
5°	246841
10°	228742
15°	203724
20°	175062
25°	148799
30°	122500
35°	95459
40°	68672
45°	43570
50°	25790
55°	17739
60°	16271
65°	15151
70°	13592
75°	12370
80°	11744
85°	10064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43570 cd/sqm



TEST NUMBER: P1255021
 CATALOG NUMBER: P3AS17R259035DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.0	9.8
10°-20°	249.1	23.4
20°-30°	281.5	26.5
30°-40°	222.6	20.9
40°-50°	112.5	10.6
50°-60°	45.0	4.2
60°-70°	28.8	2.7
70°-80°	15.9	1.5
80°-90°	4.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	634.6	59.6
0°-40°	857.2	80.6
0°-60°	1014.7	95.4
0°-90°	1064.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1153	
5°	1121	104
15°	897	249
25°	615	281
35°	357	223
45°	140	112
55°	46	45
65°	29	29
75°	15	16
85°	4	5
90°	0	



TEST NUMBER: P1255021
CATALOG NUMBER: P3AS17R259035DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1153.2
1°	1153.2
2°	1149.2
3°	1142.6
4°	1133.3
5°	1121.4
6°	1106.8
7°	1089.6
8°	1071.0
9°	1049.8
10°	1027.3
11°	1002.1
12°	978.2
13°	950.4
14°	923.9
15°	897.4
17.5°	823.1
20°	750.2
22.5°	681.3
25°	615.0
27.5°	550.1
30°	483.8
32.5°	421.5
35°	356.6
37.5°	296.9
40°	239.9
42.5°	186.9
45°	140.5
47.5°	104.7
50°	75.6
52.5°	57.0
55°	46.4
57.5°	42.4
60°	37.1
62.5°	33.1
65°	29.2
67.5°	25.2
70°	21.2
72.5°	18.6
75°	14.6
77.5°	11.9
80°	9.3
82.5°	6.6
85°	4.0
87.5°	1.3



TEST NUMBER: P1255021
CATALOG NUMBER: P3AS17R259035DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)