

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255043

Luminaire Tested: P3AS17R309035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 687.9 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255043

CATALOG NUMBER: P3AS17R309035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255043

CATALOG NUMBER: P3AS17R309035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401459
5°	382125
10°	321415
15°	231783
20°	143769
25°	81779
30°	45425
35°	24708
40°	13024
45°	7039
50°	3753
55°	2485
60°	2281
65°	2335
70°	2052
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7039 cd/sqm

TEST NUMBER: P1255043

CATALOG NUMBER: P3AS17R309035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	22.7
10°-20°	277.9	40.4
20°-30°	160.6	23.3
30°-40°	60.9	8.9
40°-50°	18.7	2.7
50°-60°	6.3	0.9
60°-70°	4.2	0.6
70°-80°	2.3	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	594.8	86.5
0°-40°	655.7	95.3
0°-60°	680.7	99.0
0°-90°	687.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1831	
5°	1736	156
15°	1021	278
25°	338	161
35°	92	61
45°	23	19
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1255043

CATALOG NUMBER: P3AS17R309035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1830.8
1°	1829.5
2°	1818.5
3°	1797.7
4°	1771.7
5°	1736.0
6°	1690.5
7°	1639.8
8°	1583.2
9°	1515.6
10°	1443.5
11°	1365.5
12°	1283.0
13°	1196.5
14°	1108.8
15°	1021.0
17.5°	805.3
20°	616.1
22.5°	456.9
25°	338.0
27.5°	245.7
30°	179.4
32.5°	129.3
35°	92.3
37.5°	64.3
40°	45.5
42.5°	31.8
45°	22.7
47.5°	15.6
50°	11.0
52.5°	7.8
55°	6.5
57.5°	5.8
60°	5.2
62.5°	4.5
65°	4.5
67.5°	3.9
70°	3.2
72.5°	2.6
75°	1.9
77.5°	1.9
80°	1.3
82.5°	1.3
85°	0.6
87.5°	0.0



TEST NUMBER: P1255043

CATALOG NUMBER: P3AS17R309035DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)