

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255059

Luminaire Tested: P3AS17R309035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1403.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255059

CATALOG NUMBER: P3AS17R309035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1255059

CATALOG NUMBER: P3AS17R309035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	818684
5°	779219
10°	655432
15°	472670
20°	293185
25°	166752
30°	92622
35°	50380
40°	26564
45°	14389
50°	7676
55°	5085
60°	4649
65°	4825
70°	4231
75°	3389
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1255059

CATALOG NUMBER: P3AS17R309035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.8	22.7
10°-20°	566.6	40.4
20°-30°	327.5	23.3
30°-40°	124.3	8.9
40°-50°	38.1	2.7
50°-60°	12.8	0.9
60°-70°	8.7	0.6
70°-80°	4.7	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1212.9	86.4
0°-40°	1337.1	95.3
0°-60°	1388.1	98.9
0°-90°	1403.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1403.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3734	
5°	3540	319
15°	2082	567
25°	689	327
35°	188	124
45°	46	38
55°	13	13
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1255059

CATALOG NUMBER: P3AS17R309035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3733.5
1°	3730.9
2°	3708.4
3°	3666.0
4°	3612.9
5°	3540.0
6°	3447.3
7°	3343.9
8°	3228.6
9°	3090.7
10°	2943.6
11°	2784.6
12°	2616.3
13°	2440.0
14°	2261.1
15°	2082.1
17.5°	1642.1
20°	1256.4
22.5°	931.7
25°	689.2
27.5°	501.0
30°	365.8
32.5°	263.7
35°	188.2
37.5°	131.2
40°	92.8
42.5°	64.9
45°	46.4
47.5°	31.8
50°	22.5
52.5°	15.9
55°	13.3
57.5°	11.9
60°	10.6
62.5°	9.3
65°	9.3
67.5°	8.0
70°	6.6
72.5°	5.3
75°	4.0
77.5°	4.0
80°	2.7
82.5°	2.7
85°	1.3
87.5°	0.0



TEST NUMBER: P1255059

CATALOG NUMBER: P3AS17R309035DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)