

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255096

Luminaire Tested: P3AS17R409035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1860.9 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255096

CATALOG NUMBER: P3AS17R409035DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1255096

CATALOG NUMBER: P3AS17R409035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85		
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82		
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79		
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76		
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73		
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	979856
5°	975146
10°	943380
15°	834625
20°	544554
25°	192906
30°	40918
35°	13465
40°	4924
45°	1644
50°	1365
55°	1529
60°	1140
65°	1349
70°	833
75°	1101
80°	1642
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 2184 cd/sqm

TEST NUMBER: P1255096

CATALOG NUMBER: P3AS17R409035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	416.8	22.4
10°-20°	970.8	52.2
20°-30°	421.2	22.6
30°-40°	38.8	2.1
40°-50°	5.5	0.3
50°-60°	3.4	0.2
60°-70°	2.4	0.1
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1808.8	97.2
0°-40°	1847.7	99.3
0°-60°	1856.6	99.8
0°-90°	1860.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1860.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4468	
5°	4430	417
15°	3676	971
25°	797	421
35°	50	39
45°	5	6
55°	4	3
65°	3	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1255096

CATALOG NUMBER: P3AS17R409035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4468.5
2.5°	4463.2
5°	4430.1
7.5°	4359.9
10°	4236.8
12.5°	4028.8
15°	3676.5
17.5°	3092.5
20°	2333.6
22.5°	1515.1
25°	797.3
27.5°	343.0
30°	161.6
32.5°	87.4
35°	50.3
37.5°	30.5
40°	17.2
42.5°	9.3
45°	5.3
47.5°	4.0
50°	4.0
52.5°	4.0
55°	4.0
57.5°	4.0
60°	2.6
62.5°	2.6
65°	2.6
67.5°	2.6
70°	1.3
72.5°	1.3
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)