

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255816

Luminaire Tested: P3AS24R459035D010 E3CD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255816  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R459035D010 E3CD1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3CD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2736.0 lumens  
Efficiency: N/A  
Efficacy: 95.0 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255816

CATALOG NUMBER: P3AS24R459035D010 E3CD1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1255816

CATALOG NUMBER: P3AS24R459035D010 E3CD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 91  |  | 94  | 91  | 89  |  | 92  |
| 4   | 102 | 95  | 91  | 87  | 100 | 94  | 90  | 87  | 92  | 89  | 86  |  | 90  | 87  | 85  |  | 88  |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 6   | 94  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  |  | 83  | 80  | 77  |  | 82  |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 78  | 74  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 67  | 65  |  | 71  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1186199 |
| 5°  | 1192535 |
| 10° | 1155890 |
| 15° | 968632  |
| 20° | 740454  |
| 25° | 450752  |
| 30° | 187548  |
| 35° | 60097   |
| 40° | 18692   |
| 45° | 3783    |
| 50° | 2797    |
| 55° | 3135    |
| 60° | 2675    |
| 65° | 3165    |
| 70° | 2629    |
| 75° | 3474    |
| 80° | 2526    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3783 cd/sqm

TEST NUMBER: P1255816

CATALOG NUMBER: P3AS24R459035D010 E3CD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 510.9  | 18.7      |
| 10°-20°   | 1172.7 | 42.9      |
| 20°-30°   | 844.4  | 30.9      |
| 30°-40°   | 175.7  | 6.4       |
| 40°-50°   | 16.1   | 0.6       |
| 50°-60°   | 6.6    | 0.2       |
| 60°-70°   | 5.3    | 0.2       |
| 70°-80°   | 3.5    | 0.1       |
| 80°-90°   | 0.8    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 2528.0 | 92.4      |
| 0°-40°    | 2703.7 | 98.8      |
| 0°-60°    | 2726.4 | 99.6      |
| 0°-90°    | 2736.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2736.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5410 |      |
| 5°  | 5418 | 511  |
| 15° | 4267 | 1173 |
| 25° | 1863 | 844  |
| 35° | 224  | 176  |
| 45° | 12   | 16   |
| 55° | 8    | 7    |
| 65° | 6    | 5    |
| 75° | 4    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1255816

CATALOG NUMBER: P3AS24R459035D010 E3CD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5409.5 |
| 2.5°  | 5411.6 |
| 5°    | 5417.7 |
| 7.5°  | 5378.9 |
| 10°   | 5191.2 |
| 12.5° | 4799.4 |
| 15°   | 4266.8 |
| 17.5° | 3722.0 |
| 20°   | 3173.1 |
| 22.5° | 2542.5 |
| 25°   | 1863.0 |
| 27.5° | 1228.4 |
| 30°   | 740.7  |
| 32.5° | 414.2  |
| 35°   | 224.5  |
| 37.5° | 126.5  |
| 40°   | 65.3   |
| 42.5° | 28.6   |
| 45°   | 12.2   |
| 47.5° | 8.2    |
| 50°   | 8.2    |
| 52.5° | 8.2    |
| 55°   | 8.2    |
| 57.5° | 6.1    |
| 60°   | 6.1    |
| 62.5° | 6.1    |
| 65°   | 6.1    |
| 67.5° | 4.1    |
| 70°   | 4.1    |
| 72.5° | 4.1    |
| 75°   | 4.1    |
| 77.5° | 2.0    |
| 80°   | 2.0    |
| 82.5° | 2.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)