

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255128

Luminaire Tested: P3AS17R459035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 725.9 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255128

CATALOG NUMBER: P3AS17R459035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255128

CATALOG NUMBER: P3AS17R459035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272632
5°	266255
10°	244752
15°	207379
20°	160897
25°	112482
30°	70846
35°	41706
40°	23616
45°	11474
50°	3991
55°	3211
60°	3114
65°	3009
70°	2885
75°	2711
80°	2399
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11474 cd/sqm

TEST NUMBER: P1255128

CATALOG NUMBER: P3AS17R459035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.0	15.4
10°-20°	250.9	34.6
20°-30°	213.0	29.3
30°-40°	101.6	14.0
40°-50°	30.6	4.2
50°-60°	7.8	1.1
60°-70°	5.8	0.8
70°-80°	3.4	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.8	79.3
0°-40°	677.5	93.3
0°-60°	715.8	98.6
0°-90°	725.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1243	
5°	1210	112
15°	914	251
25°	465	213
35°	156	102
45°	37	31
55°	8	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1255128

CATALOG NUMBER: P3AS17R459035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1243.3
2.5°	1235.5
5°	1209.6
7.5°	1164.8
10°	1099.2
12.5°	1012.2
15°	913.5
17.5°	803.8
20°	689.5
22.5°	573.3
25°	464.9
27.5°	366.2
30°	279.8
32.5°	210.4
35°	155.8
37.5°	114.9
40°	82.5
42.5°	57.1
45°	37.0
47.5°	20.8
50°	11.7
52.5°	9.1
55°	8.4
57.5°	7.8
60°	7.1
62.5°	6.5
65°	5.8
67.5°	5.2
70°	4.5
72.5°	3.9
75°	3.2
77.5°	2.6
80°	1.9
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)