

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255835

Luminaire Tested: P3AS24R459035D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R459035D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1472.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255835

CATALOG NUMBER: P3AS24R459035D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255835

CATALOG NUMBER: P3AS24R459035D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	438452
5°	428438
10°	395250
15°	343680
20°	282335
25°	219666
30°	162227
35°	114144
40°	71248
45°	38609
50°	20878
55°	17930
60°	16095
65°	13750
70°	11797
75°	12115
80°	10355
85°	10315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 38609 cd/sqm

TEST NUMBER: P1255835

CATALOG NUMBER: P3AS24R459035D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.3	12.2
10°-20°	418.5	28.4
20°-30°	415.5	28.2
30°-40°	267.6	18.2
40°-50°	103.1	7.0
50°-60°	41.9	2.8
60°-70°	26.5	1.8
70°-80°	14.3	1.0
80°-90°	4.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1014.3	68.9
0°-40°	1281.8	87.1
0°-60°	1426.8	96.9
0°-90°	1472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2000	
5°	1946	180
15°	1514	419
25°	908	415
35°	426	268
45°	124	103
55°	47	42
65°	26	26
75°	14	14
85°	4	4
90°	0	

TEST NUMBER: P1255835

CATALOG NUMBER: P3AS24R459035D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1999.5
2.5°	1989.3
5°	1946.4
7.5°	1873.0
10°	1775.1
12.5°	1652.6
15°	1513.9
17.5°	1362.9
20°	1209.9
22.5°	1054.8
25°	907.9
27.5°	769.2
30°	640.7
32.5°	528.4
35°	426.4
37.5°	334.6
40°	248.9
42.5°	179.5
45°	124.5
47.5°	83.7
50°	61.2
52.5°	51.0
55°	46.9
57.5°	40.8
60°	36.7
62.5°	30.6
65°	26.5
67.5°	22.4
70°	18.4
72.5°	16.3
75°	14.3
77.5°	10.2
80°	8.2
82.5°	6.1
85°	4.1
87.5°	2.0
90°	0.0

(END OF REPORT)