

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255147

Luminaire Tested: P3AS17R509035DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509035DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1814.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255147

CATALOG NUMBER: P3AS17R509035DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1255147

CATALOG NUMBER: P3AS17R509035DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	631770
5°	620447
10°	595758
15°	546291
20°	481712
25°	369215
30°	200765
35°	64594
40°	15171
45°	2047
50°	1808
55°	2026
60°	1754
65°	2075
70°	1731
75°	2288
80°	1642
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 3271 cd/sqm

TEST NUMBER: P1255147

CATALOG NUMBER: P3AS17R509035DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.5	14.6
10°-20°	668.9	36.9
20°-30°	669.9	36.9
30°-40°	188.4	10.4
40°-50°	11.4	0.6
50°-60°	4.3	0.2
60°-70°	3.5	0.2
70°-80°	2.3	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1603.3	88.4
0°-40°	1791.7	98.8
0°-60°	1807.4	99.6
0°-90°	1814.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1814.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2881	
5°	2819	265
15°	2406	669
25°	1526	670
35°	241	188
45°	7	11
55°	5	4
65°	4	3
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1255147

CATALOG NUMBER: P3AS17R509035DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2881.1
2.5°	2866.5
5°	2818.7
7.5°	2753.8
10°	2675.6
12.5°	2557.6
15°	2406.4
17.5°	2232.7
20°	2064.3
22.5°	1854.9
25°	1526.0
27.5°	1136.3
30°	792.9
32.5°	478.6
35°	241.3
37.5°	114.0
40°	53.0
42.5°	19.9
45°	6.6
47.5°	5.3
50°	5.3
52.5°	5.3
55°	5.3
57.5°	4.0
60°	4.0
62.5°	4.0
65°	4.0
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)