

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255216

Luminaire Tested: P3AS17R609035DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1255216  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609035DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1393.9 lumens  
Efficiency: N/A  
Efficacy: 65.8 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255216  
CATALOG NUMBER: P3AS17R609035DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1255216  
 CATALOG NUMBER: P3AS17R609035DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	329162
5°	326061
10°	316538
15°	296574
20°	262499
25°	219593
30°	172102
35°	124852
40°	83070
45°	51757
50°	28008
55°	8105
60°	7543
65°	6849
70°	6796
75°	6693
80°	6693
85°	6542

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 51757 cd/sqm



TEST NUMBER: P1255216  
 CATALOG NUMBER: P3AS17R609035DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.5	10.0
10°-20°	362.5	26.0
20°-30°	413.1	29.6
30°-40°	293.0	21.0
40°-50°	132.9	9.5
50°-60°	28.2	2.0
60°-70°	13.6	1.0
70°-80°	8.4	0.6
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.0	65.6
0°-40°	1208.0	86.7
0°-60°	1369.1	98.2
0°-90°	1393.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1501	
5°	1481	139
15°	1306	362
25°	908	413
35°	466	293
45°	167	133
55°	21	28
65°	13	14
75°	8	8
85°	3	3
90°	0	



TEST NUMBER: P1255216  
CATALOG NUMBER: P3AS17R609035DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1501.1
2.5°	1495.8
5°	1481.3
7.5°	1456.1
10°	1421.6
12.5°	1372.6
15°	1306.4
17.5°	1222.9
20°	1124.9
22.5°	1018.9
25°	907.6
27.5°	793.6
30°	679.7
32.5°	571.0
35°	466.4
37.5°	373.6
40°	290.2
42.5°	219.9
45°	166.9
47.5°	124.5
50°	82.1
52.5°	38.4
55°	21.2
57.5°	18.5
60°	17.2
62.5°	15.9
65°	13.2
67.5°	11.9
70°	10.6
72.5°	9.3
75°	7.9
77.5°	6.6
80°	5.3
82.5°	4.0
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)