

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255226

Luminaire Tested: P3AS17R609035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1092.0 lumens
Efficiency: N/A
Efficacy: 51.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255226

CATALOG NUMBER: P3AS17R609035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255226

CATALOG NUMBER: P3AS17R609035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	193844
5°	191679
10°	185033
15°	174802
20°	161131
25°	145896
30°	129539
35°	110691
40°	88022
45°	62053
50°	37082
55°	18733
60°	18025
65°	16500
70°	15323
75°	14572
80°	13386
85°	10064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 62053 cd/sqm

TEST NUMBER: P1255226

CATALOG NUMBER: P3AS17R609035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	7.5
10°-20°	215.2	19.7
20°-30°	276.3	25.3
30°-40°	256.2	23.5
40°-50°	156.0	14.3
50°-60°	52.0	4.8
60°-70°	31.6	2.9
70°-80°	17.8	1.6
80°-90°	5.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	573.4	52.5
0°-40°	829.5	76.0
0°-60°	1037.5	95.0
0°-90°	1092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	884	
5°	871	82
15°	770	215
25°	603	276
35°	414	256
45°	200	156
55°	49	52
65°	32	32
75°	17	18
85°	4	5
90°	0	

TEST NUMBER: P1255226

CATALOG NUMBER: P3AS17R609035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	884.0
2.5°	880.0
5°	870.8
7.5°	853.5
10°	831.0
12.5°	803.2
15°	770.0
17.5°	731.6
20°	690.5
22.5°	646.8
25°	603.0
27.5°	558.0
30°	511.6
32.5°	465.2
35°	413.5
37.5°	359.2
40°	307.5
42.5°	253.1
45°	200.1
47.5°	155.1
50°	108.7
52.5°	64.9
55°	49.0
57.5°	45.1
60°	41.1
62.5°	35.8
65°	31.8
67.5°	27.8
70°	23.9
72.5°	19.9
75°	17.2
77.5°	13.3
80°	10.6
82.5°	6.6
85°	4.0
87.5°	2.7
90°	0.0

(END OF REPORT)