

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255249

Luminaire Tested: P3AS17R659035DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659035DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1329.0 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255249

CATALOG NUMBER: P3AS17R659035DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255249

CATALOG NUMBER: P3AS17R659035DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313418
5°	309662
10°	297901
15°	279071
20°	250995
25°	213133
30°	166684
35°	118802
40°	77746
45°	48067
50°	24392
55°	8602
60°	7543
65°	7575
70°	6796
75°	6693
80°	6693
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48067 cd/sqm

TEST NUMBER: P1255249

CATALOG NUMBER: P3AS17R659035DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.1	9.9
10°-20°	342.1	25.7
20°-30°	399.8	30.1
30°-40°	279.4	21.0
40°-50°	123.0	9.3
50°-60°	27.4	2.1
60°-70°	13.9	1.0
70°-80°	8.4	0.6
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.0	65.8
0°-40°	1153.5	86.8
0°-60°	1303.8	98.1
0°-90°	1329.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1329.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1429	
5°	1407	132
15°	1229	342
25°	881	400
35°	444	279
45°	155	123
55°	22	27
65°	15	14
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P1255249

CATALOG NUMBER: P3AS17R659035DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1429.3
2.5°	1424.0
5°	1406.8
7.5°	1377.6
10°	1337.9
12.5°	1288.9
15°	1229.3
17.5°	1156.4
20°	1075.6
22.5°	984.2
25°	880.9
27.5°	772.3
30°	658.3
32.5°	548.4
35°	443.8
37.5°	352.4
40°	271.6
42.5°	205.3
45°	155.0
47.5°	113.9
50°	71.5
52.5°	37.1
55°	22.5
57.5°	19.9
60°	17.2
62.5°	15.9
65°	14.6
67.5°	11.9
70°	10.6
72.5°	9.3
75°	7.9
77.5°	6.6
80°	5.3
82.5°	4.0
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)