

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255250

Luminaire Tested: P3AS17R659035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 511.0 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255250

CATALOG NUMBER: P3AS17R659035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255250

CATALOG NUMBER: P3AS17R659035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90936
5°	89720
10°	86705
15°	81771
20°	75420
25°	68472
30°	60642
35°	51584
40°	41048
45°	28995
50°	16818
55°	9175
60°	8552
65°	7731
70°	7052
75°	6608
80°	5683
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28995 cd/sqm

TEST NUMBER: P1255250

CATALOG NUMBER: P3AS17R659035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	7.5
10°-20°	100.8	19.7
20°-30°	129.5	25.3
30°-40°	119.8	23.4
40°-50°	72.3	14.2
50°-60°	24.7	4.8
60°-70°	14.8	2.9
70°-80°	8.4	1.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.6	52.6
0°-40°	388.4	76.0
0°-60°	485.4	95.0
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	415	
5°	408	38
15°	360	101
25°	283	130
35°	193	120
45°	94	72
55°	24	25
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1255250

CATALOG NUMBER: P3AS17R659035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.7
2.5°	412.7
5°	407.6
7.5°	399.8
10°	389.4
12.5°	376.4
15°	360.2
17.5°	342.7
20°	323.2
22.5°	303.1
25°	283.0
27.5°	261.5
30°	239.5
32.5°	217.4
35°	192.7
37.5°	168.7
40°	143.4
42.5°	118.1
45°	93.5
47.5°	70.7
50°	49.3
52.5°	31.2
55°	24.0
57.5°	21.4
60°	19.5
62.5°	16.9
65°	14.9
67.5°	13.0
70°	11.0
72.5°	9.7
75°	7.8
77.5°	6.5
80°	4.5
82.5°	3.2
85°	1.9
87.5°	1.3
90°	0.0

(END OF REPORT)