

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255974

Luminaire Tested: P3AS24R709035D010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1255974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R709035D010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1467.0 lumens  
Efficiency: N/A  
Efficacy: 50.9 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255974  
CATALOG NUMBER: P3AS24R709035D010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1255974  
 CATALOG NUMBER: P3AS24R709035D010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	344095
5°	337772
10°	318520
15°	289060
20°	252862
25°	213278
30°	174634
35°	135479
40°	96953
45°	61371
50°	30634
55°	18733
60°	16095
65°	14839
70°	13079
75°	12115
80°	10355
85°	10315

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 61371 cd/sqm



TEST NUMBER: P1255974  
 CATALOG NUMBER: P3AS24R709035D010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.2	9.8
10°-20°	354.3	24.2
20°-30°	403.5	27.5
30°-40°	315.6	21.5
40°-50°	155.0	10.6
50°-60°	47.7	3.3
60°-70°	28.2	1.9
70°-80°	15.1	1.0
80°-90°	4.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.0	61.4
0°-40°	1216.6	82.9
0°-60°	1419.2	96.7
0°-90°	1467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1467.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1569	
5°	1534	143
15°	1273	354
25°	882	404
35°	506	316
45°	198	155
55°	49	48
65°	29	28
75°	14	15
85°	4	4
90°	0	



TEST NUMBER: P1255974  
CATALOG NUMBER: P3AS24R709035D010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1569.2
2.5°	1561.1
5°	1534.5
7.5°	1491.7
10°	1430.5
12.5°	1359.0
15°	1273.3
17.5°	1181.5
20°	1083.6
22.5°	981.5
25°	881.5
27.5°	783.6
30°	689.7
32.5°	595.9
35°	506.1
37.5°	420.4
40°	338.7
42.5°	263.2
45°	197.9
47.5°	138.8
50°	89.8
52.5°	59.2
55°	49.0
57.5°	42.9
60°	36.7
62.5°	32.6
65°	28.6
67.5°	24.5
70°	20.4
72.5°	16.3
75°	14.3
77.5°	12.2
80°	8.2
82.5°	6.1
85°	4.1
87.5°	2.0
90°	0.0

(END OF REPORT)