

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256044

Luminaire Tested: P3AS02R109040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 189.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256044

CATALOG NUMBER: P3AS02R109040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256044

CATALOG NUMBER: P3AS02R109040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		92
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		83
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		76
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		70
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		65
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		60
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		56
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		49
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47672
5°	46379
10°	42373
15°	37117
20°	31853
25°	26590
30°	21269
35°	15954
40°	11593
45°	7567
50°	4742
55°	3211
60°	2851
65°	2594
70°	2436
75°	2203
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7567 cd/sqm

TEST NUMBER: P1256044

CATALOG NUMBER: P3AS02R109040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.4	10.3
10°-20°	45.6	24.1
20°-30°	50.2	26.6
30°-40°	37.6	19.9
40°-50°	19.5	10.3
50°-60°	8.1	4.3
60°-70°	5.0	2.6
70°-80°	2.8	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.2	61.0
0°-40°	152.8	80.9
0°-60°	180.4	95.5
0°-90°	189.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	189.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	211	19
15°	164	46
25°	110	50
35°	60	38
45°	24	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256044

CATALOG NUMBER: P3AS02R109040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.4
1°	217.6
2°	216.9
3°	215.5
4°	213.3
5°	210.7
6°	207.3
7°	203.8
8°	199.4
9°	194.9
10°	190.3
12.5°	177.2
15°	163.5
17.5°	149.9
20°	136.5
22.5°	122.8
25°	109.9
27.5°	97.0
30°	84.0
32.5°	71.4
35°	59.6
37.5°	49.6
40°	40.5
42.5°	32.1
45°	24.4
47.5°	18.4
50°	13.9
52.5°	10.3
55°	8.4
57.5°	7.4
60°	6.5
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.8
72.5°	3.1
75°	2.6
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)