

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256070

Luminaire Tested: P3AS02R129040DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129040DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 264.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256070

CATALOG NUMBER: P3AS02R129040DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1256070

CATALOG NUMBER: P3AS02R129040DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225530
5°	200198
10°	139031
15°	82225
20°	46834
25°	26760
30°	14812
35°	7897
40°	4380
45°	2357
50°	1467
55°	1185
60°	1009
65°	934
70°	833
75°	847
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2357 cd/sqm

TEST NUMBER: P1256070

CATALOG NUMBER: P3AS02R129040DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	29.3
10°-20°	102.1	38.7
20°-30°	52.5	19.9
30°-40°	19.7	7.5
40°-50°	6.4	2.4
50°-60°	2.8	1.1
60°-70°	1.8	0.7
70°-80°	1.1	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.0	87.9
0°-40°	251.7	95.3
0°-60°	260.9	98.8
0°-90°	264.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	264.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1028	
5°	910	77
15°	362	102
25°	111	53
35°	30	20
45°	8	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256070

CATALOG NUMBER: P3AS02R129040DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1028.5
1°	1026.4
2°	1013.0
3°	987.3
4°	953.5
5°	909.5
6°	859.6
7°	804.9
8°	744.1
9°	684.1
10°	624.4
12.5°	480.4
15°	362.2
17.5°	271.1
20°	200.7
22.5°	149.8
25°	110.6
27.5°	80.6
30°	58.5
32.5°	41.5
35°	29.5
37.5°	21.1
40°	15.3
42.5°	10.9
45°	7.6
47.5°	5.6
50°	4.3
52.5°	3.6
55°	3.1
57.5°	2.5
60°	2.3
62.5°	2.0
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)