

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256079

Luminaire Tested: P3AS02R129040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256079

CATALOG NUMBER: P3AS02R129040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256079

CATALOG NUMBER: P3AS02R129040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	73		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67692
5°	62580
10°	49966
15°	37730
20°	28726
25°	21896
30°	15699
35°	10226
40°	6269
45°	3783
50°	2524
55°	1950
60°	1667
65°	1453
70°	1282
75°	1271
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3783 cd/sqm

TEST NUMBER: P1256079

CATALOG NUMBER: P3AS02R129040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	16.0
10°-20°	46.5	29.6
20°-30°	41.4	26.4
30°-40°	24.5	15.6
40°-50°	10.0	6.4
50°-60°	4.7	3.0
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.0	72.0
0°-40°	137.5	87.6
0°-60°	152.2	97.0
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	309	
5°	284	25
15°	166	46
25°	90	41
35°	38	24
45°	12	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1256079

CATALOG NUMBER: P3AS02R129040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	308.7
1°	308.0
2°	305.7
3°	301.1
4°	293.4
5°	284.3
6°	274.3
7°	262.6
8°	250.4
9°	237.9
10°	224.4
12.5°	193.5
15°	166.2
17.5°	142.8
20°	123.1
22.5°	105.8
25°	90.5
27.5°	75.7
30°	62.0
32.5°	49.5
35°	38.2
37.5°	29.3
40°	21.9
42.5°	16.3
45°	12.2
47.5°	9.4
50°	7.4
52.5°	6.1
55°	5.1
57.5°	4.3
60°	3.8
62.5°	3.3
65°	2.8
67.5°	2.5
70°	2.0
72.5°	1.8
75°	1.5
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)