

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255291

Luminaire Tested: P3AS20R159035D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159035D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2200.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255291

CATALOG NUMBER: P3AS20R159035D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1255291

CATALOG NUMBER: P3AS20R159035D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96		
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92		
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91		
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89		
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88		
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86		
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85		
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4276280
5°	3583944
10°	1688167
15°	508970
20°	188316
25°	73214
30°	27295
35°	8379
40°	2977
45°	1613
50°	1194
55°	1338
60°	1535
65°	882
70°	1090
75°	1440
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1613 cd/sqm

TEST NUMBER: P1255291

CATALOG NUMBER: P3AS20R159035D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1258.7	57.2
10°-20°	748.2	34.0
20°-30°	157.2	7.1
30°-40°	25.3	1.2
40°-50°	4.3	0.2
50°-60°	3.1	0.1
60°-70°	1.9	0.1
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2164.1	98.4
0°-40°	2189.5	99.5
0°-60°	2196.9	99.9
0°-90°	2200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2200.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19501	
5°	16282	###
15°	2242	748
25°	303	157
35°	31	25
45°	5	4
55°	4	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1255291

CATALOG NUMBER: P3AS20R159035D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	19501.4
1°	19440.5
2°	19130.9
3°	18511.7
4°	17603.8
5°	16281.9
6°	14728.6
7°	12952.8
8°	11256.9
9°	9336.7
10°	7581.7
12.5°	4090.9
15°	2242.0
17.5°	1313.2
20°	807.0
22.5°	494.0
25°	302.6
27.5°	182.6
30°	107.8
32.5°	60.9
35°	31.3
37.5°	17.4
40°	10.4
42.5°	7.0
45°	5.2
47.5°	3.5
50°	3.5
52.5°	3.5
55°	3.5
57.5°	3.5
60°	3.5
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)