

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255324

Luminaire Tested: P3AS20R209035D010 E3CD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255324  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209035D010 E3CD1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3CD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2197.0 lumens  
Efficiency: N/A  
Efficacy: 76.3 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255324

CATALOG NUMBER: P3AS20R209035D010 E3CD1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1255324

CATALOG NUMBER: P3AS20R209035D010 E3CD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 110 | 113 | 112 | 110 | 109 | 108 | 106 | 105 |  | 104 | 103 | 102 |  | 101 |
| 2   | 112 | 109 | 107 | 104 | 110 | 108 | 105 | 103 | 104 | 103 | 101 |  | 102 | 100 | 99  |  | 99  |
| 3   | 109 | 105 | 102 | 100 | 108 | 104 | 101 | 99  | 102 | 99  | 97  |  | 99  | 98  | 96  |  | 97  |
| 4   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  |  | 97  | 95  | 93  |  | 96  |
| 5   | 104 | 99  | 96  | 93  | 103 | 98  | 95  | 93  | 97  | 94  | 92  |  | 95  | 93  | 91  |  | 94  |
| 6   | 102 | 97  | 93  | 91  | 101 | 96  | 93  | 90  | 95  | 92  | 90  |  | 94  | 91  | 89  |  | 93  |
| 7   | 100 | 94  | 91  | 88  | 99  | 94  | 91  | 88  | 93  | 90  | 88  |  | 92  | 89  | 87  |  | 91  |
| 8   | 98  | 92  | 89  | 86  | 97  | 92  | 89  | 86  | 91  | 88  | 86  |  | 90  | 88  | 86  |  | 89  |
| 9   | 96  | 90  | 87  | 85  | 95  | 90  | 87  | 85  | 89  | 86  | 84  |  | 89  | 86  | 84  |  | 88  |
| 10  | 94  | 89  | 85  | 83  | 93  | 88  | 85  | 83  | 88  | 85  | 83  |  | 87  | 84  | 83  |  | 87  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3412183 |
| 5°  | 2961670 |
| 10° | 1830004 |
| 15° | 635600  |
| 20° | 195200  |
| 25° | 69004   |
| 30° | 25548   |
| 35° | 10253   |
| 40° | 5467    |
| 45° | 2171    |
| 50° | 1194    |
| 55° | 1338    |
| 60° | 1535    |
| 65° | 882     |
| 70° | 1090    |
| 75° | 1440    |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2171 cd/sqm

TEST NUMBER: P1255324

CATALOG NUMBER: P3AS20R209035D010 E3CD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1116.7 | 50.8      |
| 10°-20°   | 886.0  | 40.3      |
| 20°-30°   | 153.4  | 7.0       |
| 30°-40°   | 27.9   | 1.3       |
| 40°-50°   | 6.4    | 0.3       |
| 50°-60°   | 3.1    | 0.1       |
| 60°-70°   | 1.9    | 0.1       |
| 70°-80°   | 1.6    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 2156.1 | 98.1      |
| 0°-40°    | 2184.0 | 99.4      |
| 0°-60°    | 2193.5 | 99.8      |
| 0°-90°    | 2197.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2197.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 15561 |      |
| 5°  | 13455 | ###  |
| 15° | 2800  | 886  |
| 25° | 285   | 153  |
| 35° | 38    | 28   |
| 45° | 7     | 6    |
| 55° | 4     | 3    |
| 65° | 2     | 2    |
| 75° | 2     | 2    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1255324

CATALOG NUMBER: P3AS20R209035D010 E3CD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 15560.8 |
| 1°    | 15486.1 |
| 2°    | 15190.4 |
| 3°    | 14715.7 |
| 4°    | 14159.2 |
| 5°    | 13454.9 |
| 6°    | 12648.0 |
| 7°    | 11708.9 |
| 8°    | 10639.4 |
| 9°    | 9437.7  |
| 10°   | 8218.7  |
| 12.5° | 5184.0  |
| 15°   | 2799.8  |
| 17.5° | 1495.6  |
| 20°   | 836.5   |
| 22.5° | 478.2   |
| 25°   | 285.2   |
| 27.5° | 173.9   |
| 30°   | 100.9   |
| 32.5° | 59.1    |
| 35°   | 38.3    |
| 37.5° | 26.1    |
| 40°   | 19.1    |
| 42.5° | 12.2    |
| 45°   | 7.0     |
| 47.5° | 3.5     |
| 50°   | 3.5     |
| 52.5° | 3.5     |
| 55°   | 3.5     |
| 57.5° | 3.5     |
| 60°   | 3.5     |
| 62.5° | 1.7     |
| 65°   | 1.7     |
| 67.5° | 1.7     |
| 70°   | 1.7     |
| 72.5° | 1.7     |
| 75°   | 1.7     |
| 77.5° | 1.7     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |

(END OF REPORT)