

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256111

Luminaire Tested: P3AS02R159040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 161.0 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256111

CATALOG NUMBER: P3AS02R159040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256111

CATALOG NUMBER: P3AS02R159040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69424
5°	64164
10°	51235
15°	38706
20°	29473
25°	22453
30°	16078
35°	10494
40°	6441
45°	3876
50°	2593
55°	1988
60°	1710
65°	1505
70°	1346
75°	1356
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3876 cd/sqm

TEST NUMBER: P1256111

CATALOG NUMBER: P3AS02R159040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	16.0
10°-20°	47.6	29.6
20°-30°	42.4	26.3
30°-40°	25.1	15.6
40°-50°	10.3	6.4
50°-60°	4.8	3.0
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.9	72.0
0°-40°	141.0	87.6
0°-60°	156.1	97.0
0°-90°	161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	161.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	317	
5°	292	26
15°	170	48
25°	93	42
35°	39	25
45°	12	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1256111

CATALOG NUMBER: P3AS02R159040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	316.6
1°	315.8
2°	313.5
3°	308.8
4°	300.9
5°	291.5
6°	281.3
7°	269.3
8°	256.7
9°	243.9
10°	230.1
12.5°	198.4
15°	170.5
17.5°	146.4
20°	126.3
22.5°	108.5
25°	92.8
27.5°	77.6
30°	63.5
32.5°	50.7
35°	39.2
37.5°	30.1
40°	22.5
42.5°	16.7
45°	12.5
47.5°	9.7
50°	7.6
52.5°	6.3
55°	5.2
57.5°	4.4
60°	3.9
62.5°	3.4
65°	2.9
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)