

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256125

Luminaire Tested: P3AS02R209040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 329.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256125

CATALOG NUMBER: P3AS02R209040DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256125

CATALOG NUMBER: P3AS02R209040DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	499061
5°	420184
10°	262453
15°	98116
20°	33673
25°	14033
30°	6609
35°	2971
40°	1403
45°	713
50°	273
55°	38
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1256125

CATALOG NUMBER: P3AS02R209040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	48.3
10°-20°	130.8	39.7
20°-30°	29.7	9.0
30°-40°	7.6	2.3
40°-50°	1.9	0.6
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.2	97.0
0°-40°	326.8	99.3
0°-60°	328.9	100.0
0°-90°	329.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	329.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2276	
5°	1909	159
15°	432	131
25°	58	30
35°	11	8
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256125

CATALOG NUMBER: P3AS02R209040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2275.9
1°	2256.6
2°	2199.8
3°	2118.2
4°	2018.1
5°	1908.9
6°	1787.2
7°	1652.9
8°	1496.3
9°	1341.0
10°	1178.7
11°	1005.9
12°	833.4
13°	687.3
14°	547.6
15°	432.2
16°	341.1
17°	269.1
18°	216.2
19°	175.8
20°	144.3
21°	120.7
22°	100.7
23°	83.7
24°	69.8
25°	58.0
27.5°	37.9
30°	26.1
32.5°	16.1
35°	11.1
37.5°	7.1
40°	4.9
42.5°	3.3
45°	2.3
47.5°	1.5
50°	0.8
52.5°	0.4
55°	0.1
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1256125
CATALOG NUMBER: P3AS02R209040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)