

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256126

Luminaire Tested: P3AS02R209040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 133.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256126

CATALOG NUMBER: P3AS02R209040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256126

CATALOG NUMBER: P3AS02R209040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102338
5°	93022
10°	68736
15°	42520
20°	24292
25°	13864
30°	7773
35°	4230
40°	2319
45°	1271
50°	751
55°	535
60°	526
65°	467
70°	385
75°	424
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1271 cd/sqm

TEST NUMBER: P1256126

CATALOG NUMBER: P3AS02R209040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	27.5
10°-20°	52.2	39.3
20°-30°	27.3	20.5
30°-40°	10.5	7.9
40°-50°	3.4	2.6
50°-60°	1.4	1.0
60°-70°	0.9	0.7
70°-80°	0.5	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.1	87.3
0°-40°	126.6	95.2
0°-60°	131.4	98.8
0°-90°	133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	423	37
15°	187	52
25°	57	27
35°	16	11
45°	4	3
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1256126

CATALOG NUMBER: P3AS02R209040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	466.7
1°	465.8
2°	460.2
3°	451.8
4°	438.6
5°	422.6
6°	403.6
7°	382.5
8°	358.1
9°	334.3
10°	308.7
12.5°	245.4
15°	187.3
17.5°	140.2
20°	104.1
22.5°	77.1
25°	57.3
27.5°	42.3
30°	30.7
32.5°	22.2
35°	15.8
37.5°	11.4
40°	8.1
42.5°	5.8
45°	4.1
47.5°	3.0
50°	2.2
52.5°	1.7
55°	1.4
57.5°	1.3
60°	1.2
62.5°	1.0
65°	0.9
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.3
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)