

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256127

Luminaire Tested: P3AS02R209040DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1256127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209040DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 271.0 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1256127

CATALOG NUMBER: P3AS02R209040DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1256127

CATALOG NUMBER: P3AS02R209040DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 30  |     |     |  |     | 10  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 110 | 106 | 102 | 100 |  | 108 | 104 | 101 | 98  |  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 94  | 92  |
| 3   | 106 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 97  | 93  | 91  |  | 94  | 92  | 89  |  | 92  | 90  | 88  |
| 4   | 102 | 96  | 91  | 88  |  | 100 | 95  | 90  | 87  |  | 92  | 89  | 86  |  | 91  | 88  | 85  |  | 89  | 86  | 84  |
| 5   | 98  | 91  | 87  | 83  |  | 97  | 90  | 86  | 83  |  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 86  | 83  | 81  |
| 6   | 95  | 87  | 83  | 79  |  | 93  | 87  | 82  | 79  |  | 85  | 81  | 78  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |
| 7   | 91  | 84  | 79  | 76  |  | 90  | 83  | 79  | 76  |  | 82  | 78  | 75  |  | 81  | 78  | 75  |  | 80  | 77  | 75  |
| 8   | 88  | 81  | 76  | 73  |  | 87  | 80  | 76  | 73  |  | 79  | 75  | 72  |  | 78  | 75  | 72  |  | 78  | 74  | 72  |
| 9   | 85  | 78  | 73  | 70  |  | 85  | 77  | 73  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 69  |  | 75  | 72  | 69  |
| 10  | 83  | 75  | 71  | 68  |  | 82  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 70  | 67  |  | 73  | 69  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 208514 |
| 5°  | 189544 |
| 10° | 140078 |
| 15° | 86652  |
| 20° | 49494  |
| 25° | 28260  |
| 30° | 15851  |
| 35° | 8620   |
| 40° | 4723   |
| 45° | 2605   |
| 50° | 1535   |
| 55° | 1109   |
| 60° | 1053   |
| 65° | 934    |
| 70° | 833    |
| 75° | 847    |
| 80° | 631    |
| 85° | 755    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2605 cd/sqm

TEST NUMBER: P1256127

CATALOG NUMBER: P3AS02R209040DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 74.6   | 27.5      |
| 10°-20°   | 106.4  | 39.3      |
| 20°-30°   | 55.6   | 20.5      |
| 30°-40°   | 21.5   | 7.9       |
| 40°-50°   | 7.0    | 2.6       |
| 50°-60°   | 2.8    | 1.0       |
| 60°-70°   | 1.8    | 0.7       |
| 70°-80°   | 1.1    | 0.4       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 236.6  | 87.3      |
| 0°-40°    | 258.1  | 95.2      |
| 0°-60°    | 267.8  | 98.8      |
| 0°-90°    | 271.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 271.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 951 |      |
| 5°  | 861 | 75   |
| 15° | 382 | 106  |
| 25° | 117 | 56   |
| 35° | 32  | 21   |
| 45° | 8   | 7    |
| 55° | 3   | 3    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1256127

CATALOG NUMBER: P3AS02R209040DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 950.9 |
| 1°    | 949.0 |
| 2°    | 937.8 |
| 3°    | 920.5 |
| 4°    | 893.8 |
| 5°    | 861.1 |
| 6°    | 822.3 |
| 7°    | 779.4 |
| 8°    | 729.6 |
| 9°    | 681.2 |
| 10°   | 629.1 |
| 12.5° | 500.0 |
| 15°   | 381.7 |
| 17.5° | 285.6 |
| 20°   | 212.1 |
| 22.5° | 157.1 |
| 25°   | 116.8 |
| 27.5° | 86.1  |
| 30°   | 62.6  |
| 32.5° | 45.3  |
| 35°   | 32.2  |
| 37.5° | 23.3  |
| 40°   | 16.5  |
| 42.5° | 11.8  |
| 45°   | 8.4   |
| 47.5° | 6.0   |
| 50°   | 4.5   |
| 52.5° | 3.4   |
| 55°   | 2.9   |
| 57.5° | 2.6   |
| 60°   | 2.4   |
| 62.5° | 2.1   |
| 65°   | 1.8   |
| 67.5° | 1.6   |
| 70°   | 1.3   |
| 72.5° | 1.3   |
| 75°   | 1.0   |
| 77.5° | 0.8   |
| 80°   | 0.5   |
| 82.5° | 0.5   |
| 85°   | 0.3   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)